


## CP® AERIAL NOZZLE FLOW RATES

### HANDLE PLACEMENT



### CP® NOZZLE FLOW RATE—POLY BODIES

(flow rates for all CP nozzles made with CPA203-B body)

PSI	Orifice .062	Orifice .078	Orifice .093*	Orifice .125	Orifice .172
30	0.48	0.84	1.15	2.24	3.82
40	0.58	0.97	1.33	2.60	4.50
50	0.66	1.07	1.49	2.97	4.91
60	0.72	1.19	1.63	3.19	5.30

\* Special Variation



### CP® NOZZLE FLOW RATE—STAINLESS BODIES

(flow rates for all CP nozzles made with CPA201 body)

PSI	Orifice .062	Orifice .078	Orifice .093*	Orifice .125	Orifice .172
30	0.48	0.68	0.97	1.78	2.85
40	0.58	0.79	1.15	2.00	3.30
50	0.66	0.89	1.29	2.30	3.63
60	0.72	0.98	1.41	2.50	3.95

\* Special Variation

Visit us at

[www.CPProductsInc.com](http://www.CPProductsInc.com)

For Droplet Spectrum Models, Part Information  
And so Much More!  
Or call!

Toll Free 866 303-0600

